




Base Unit Configuration Product Instructions

Online Instructions: <http://tc.help>



Quick Setup Overview



≠ INDICATES QUICK CHANGE KNOB can be used in place of the standard nut and bolt. This part will be moved for future configurations.

∞ INDICATES THAT THE PART can be attached in multiple ways or locations. Use the FIG illustration as a basic guide, but the part will be moved for future configurations.




FIG. 1



FIG. 1a




FIG.1 and FIG 1a Attach (2) L Hinges to (1) Base Bar, using ≠bolts and screws provided.

Repeat for second Base Bar

FIG. 2 Use provided ≠bolts and screws to attach (1) Primary Vertical Bar to L Hinge, on (1) Base Bar.

Repeat for second Base Bar.



FIG. 2

FIG. 3 Attach (Top) ∞Flat Stabilizing Bar onto PRIMARY VERTICAL BARS. Attach Stabilizing bar to the third hole on PRIMARY VERTICAL BARS, then secure in place with provided ≠bolt and screw.



FIG. 3




FIG. 3a




FIG. 4

FIG. 4 Attach (2) U Clips to both sides of (1) Anchor Bar.

Repeat for second Anchor Bar.



FIG. 5

FIG. 5a (Easy Roller Upgrade)

Attach (1) Anchor Bar to Primary Vertical Bar and (1) Base Bar using (1) U Clip, and #bolts and screws provided.

Repeat for second Anchor Bar.

Attach (Bottom) ∞Flat Stabilizing Bar onto Base Bars. Slide Flat Stabilizing bar up to the 2nd hole on Base Bars, then secure in place with provided #bolt and screw, and black plastic end caps as shown in FIG 5*.

*If Easy Roller Upgrade was **NOT** purchased, attach Base Bar Flat Stabilizer Bar so that round ends align to at least the second holes of Base Bar.

If Easy Roller Upgrade was purchased, attach wheels to Flat Stabilizing Bars as shown in FIG. 5a, then attach to Flat Stabilizer Bar and Wheels to Base Bar.

Parts List

QTY	ALLN-1 Bench Parts	Part Number	Notes
2	48" Perforated Tubing (Primary Base Bars)	TUB-48	
2	33" Perforated Tubing (Anchor Bars)	TUB-33	
2	30" Perforated Tubing (Primary Vertical Bars)	TUB-30	
3	28.25" Flat Stabilizing Bar	FSB-03	
4	Single U Clips	SUC-4	
4	L- Hinge Brackets	LHB-4	
	Nuts & Bolts		
14	3/8 2.5" Bolts	B3/8-25	
16	3/8 Nuts	N3/8-25	6 are for Eye Bolts
28	3/8 Washers	W3/8-25	
2	Male & Female Quick Change Knobs	MF3/8-25	
	Accessories		
2	2.5" Eye Bolts	EB3/8-25	
4	Black Caps	BC25	
2	ALLN-1 Decals		
2	Neoprene Arm Pads		
	Easy Roller Upgrade (Optional)		
2	Wheels	W01	
2	5/16 2.5" Bolts	B5/16-25	
4	5/16 Washers	W5/16	
2	5/16 Wingnuts	WN5/16	Replaced with standard nuts.

